




A full line of restorative solutions to help fit your unique needs.

With a rich legacy of oral care products and services, 3M is one of the world's most trusted companies. 3M™ Filtek™ Restoratives have been used in more than 1 billion restorations worldwide. Our family of Filtek™ Dental Restoratives lets you choose just the right option to fit any patient situation – from highly esthetic, to highly simple for an easier day.

Versatility & Esthetics		Esthetics & Simplicity	Efficiency & Simplicity		
<p>3M™ Filtek™ Supreme Ultra Universal Restorative</p> <ul style="list-style-type: none"> • Exceptional esthetics • Natural-looking fluorescence • Excellent polish retention • Exceptional handling • Outstanding strength for anterior and posterior • Wear resistance similar to enamel¹ • Can be safely warmed² and injection moulded • TRUE nanotechnology • 36 shades, 4 opacities 	<p>3M™ Filtek™ Supreme Flowable Restorative</p> <ul style="list-style-type: none"> • Virtually no bubbles or material “run-on” • Easy-to-bend cannula for improved access • Ergonomic design is easy to hold and inject • Excellent adaptation, polish retention and wear resistance • Can be safely warmed³ and injection moulded • 12 shades 	<p>3M™ Filtek™ Universal Restorative</p> <ul style="list-style-type: none"> • Predictable, repeatable esthetics • Long-lasting polish • Excellent, creamy handling • Low shrinkage stress/stress relief • Excellent wear resistance • Can be safely warmed² and injection moulded • TRUE nanotechnology • 8 designer shades plus an Extra White (XW) cover the 19 VITA® classical and bleach shades⁴ • Pink Opaquer with excellent masking ability 	<p>3M™ Filtek™ One Bulk Fill Restorative</p> <ul style="list-style-type: none"> • Increased opacity for improved esthetics • One-step placement up to 5 mm • Excellent handling • Excellent adaptation • Stress relief • Excellent wear resistance • Can be safely warmed² and injection moulded • TRUE nanotechnology • 5 shades 	<p>3M™ Filtek™ Bulk Fill Flowable Restorative</p> <ul style="list-style-type: none"> • Virtually no bubbles or material “run-on” • Easy-to-bend cannula for improved access • Ergonomic design is easy to hold and inject • Injectable, one-step placement up to 4 mm • Excellent adaptation, polish retention and low shrinkage • Can be safely warmed³ and injection moulded • 4 shades 	
					





¹ In vitro data on file.

² Warm capsules to 70°C (158°F) for up to 1 hour.

³ No higher than 70°C (158°F), no longer than 1 hour; up to 25 times, for syringes only.

⁴ 3M internal data.

We have you covered for every class of direct restoration.

	Versatility & Esthetics		Esthetics & Simplicity	Efficiency & Simplicity	
	3M™ Filtek™ Supreme Ultra Universal Restorative (Incremental up to 2 mm)	3M™ Filtek™ Supreme Flowable Restorative (Incremental up to 2 mm)	3M™ Filtek™ Universal Restorative (Incremental up to 2 mm)	3M™ Filtek™ One Bulk Fill Restorative (Bulk up to 5 mm)	3M™ Filtek™ Bulk Fill Flowable Restorative (Incremental up to 4 mm)
Class I 	✓	✓ (Liner/Base)	✓	✓ (up to 4 mm)	✓ (Liner/Base)
Class II 	✓	✓ (Liner/Base)	✓	✓ (up to 5 mm)	✓ (Liner/Base)
Class III 	✓	✓	✓		✓
Class IV 	✓		✓		
Class V 	✓	✓	✓		✓
Minimally Invasive	✓	✓	✓	✓	✓
Stress Bearing	✓		✓	✓	

✓ = recommended use

Refer to Instructions for Use for full list of indications.



Available in Canada from

3M Canada
3M Oral Care
 300 Tartan Drive
 London, ON N5V 4M9
 Canada
 1-888-363-3685
 3M.ca/dental

3M ESPE Dental Products
 2510 Conway Avenue
 St. Paul, MN 55144
 USA
 1-800-634-2249

www.3M.ca/Filtek

3M, Filtek and ESPE are trademarks of 3M or 3M Deutschland GmbH. Used under license in Canada. © 2020, 3M. All rights reserved. All other trade names referenced are the service marks, trademarks or registered trademarks of their respective companies. 2002-16658 E