

Digital Impression with Dentsply Sirona

The right choice for all
your digital needs



dentsplysirona.com/digital-impression

THE DENTAL
SOLUTIONS
COMPANY™

 Dentsply
Sirona


Digital Impression with Dentsply Sirona

Provides you with flexible workflow options to elevate your patients' experience and prepare your practice for long-term growth.

Primescan and Omnicam 2.0 are the perfect starting point into digital dentistry. While easy to use they also provide you with the flexibility to design your individual workflows and enable you to expand your treatment options in the fields of Restorative, Implantology, Orthodontics and Sleep Appliances.



SCAN ○ ○ CONNECT ○ ○ TREAT



Seamless
Connection



Validated
Workflows



Open STL
File Export

Restorative
Implantology
Orthodontics
Sleep Appliance

Grow your practice

Both, Primescan and Omnicam are a door opener to all relevant digital workflows. Going digital in your everyday work means you expand possible treatment areas within your practice and ensure greater satisfaction for your patients while at the same time growing your business.

Impress your patients with fast and pleasant intraoral scans in seconds

Enhance your practice value with Dentsply Sirona, by having all workflows out of one hand

Improve communication with patients and lab partners

Increase practice efficiency by delegating easy and intuitive impression taking

More than
75%

of patients are likely to have more preventative treatments as well as more elective procedures if digital technology played a role in their visit.¹

80%

would feel more confident they are getting the best possible dental care if digital technology, such as a 3D intraoral scanner or 3D x-ray, were used in the practice.¹

Study shows

84%

of patients preferred digital to conventional impression taking.²

¹ Patient Perceptions Quantitative Research, May 2020 - USA

² Haddadi Y, Bahrami G, Isidor F, Evaluation of Operating Time and Patient Perception Using Conventional Impression Taking and Intraoral Scanning for Crown Manufacture: A Split-mouth, Randomized Clinical Study. Int J Prosthodont 2018;31(31):55-59



"I have been using my Omnicam for 5 years with great success to treat my patients in all my working areas: restorative, implants, ortho and sleep. The decision for the new Primescan was based on its performance. It brought even greater speed and accuracy. A great advantage of Dentsply Sirona intraoral scanners is the Connect Case Center. It enables a fast and assertive communication with my lab, adding tremendous value to my daily work and providing even greater satisfaction and enchantment to my patients."

Dr. Luciana Sargologos | São Paulo, Brazil

Freedom of collaboration. Secure Data transmission with the Connect Case Center.

No matter if you start your workflow with Primescan or Omnicam, if you prefer to transmit your data securely and if desired also anonymized you can use the Connect Case Center: Dentsply Sirona's unique portal for fast and easy collaboration. It only takes a single click and your laboratory or partner receives complete case information immediately. All Dentsply Sirona scanners include a Connect Case Center Inbox license, you can give to a laboratory or partner of your choice. And you can also transfer the data with open STL format.

ENHANCED COMMUNICATION. NO ADDITIONAL COSTS.

- Simple and safe data transfer within seconds compliant to HIPPA and GDPR.
- The dental laboratory receives information immediately by e-mail confirming receipt of the order.
- Review and discussion of the 3D model on the screen simultaneously during the patient consultation allowing for an immediate correction of the impression or the preparation without the need for an additional appointment.
- Convenient transmission of additional data (patient images, screen shots, etc.).
- No license fees.



“By using the digital impressions, there is no loss of time for us as a laboratory. With Primescan and Omnicam distorted impressions are a thing of the past. Both scanners are of exceptional quality. But the accuracy of Primescan is really impressive. This makes it easy to create accurate dental restorations working directly with the original data without creating a physical working model.”

Ulrich Thielen | Master dental technician | Germany

Connectivity opens a world of possibilities


Digitize your workflows while keeping your established relationships. Your lab technician will appreciate the great scan results and easy data communication for all restorative indications as well as for all other application areas.



Send the data to your specialized partners to order orthodontic appliances, take advantage of a seamless workflow with SureSmile® aligners for a short and efficient treatment or send your scans from Omnicam to the most common aligner provider. Support your diagnosis with CEREC Ortho Software's automatic model analysis and help your patients make their treatment decision with a simulation right after the scan.



A great option. You can expand any Dentsply Sirona scanner into a CEREC System at any time and offer your patients high-quality dental restorations in a single visit.





PATIENT MONITORING



Make the most of your intraoral scanner and visualize volumetric changes in the soft tissue, hard tissue and the position of the teeth over time. OraCheck provides a 3D comparison between two or more digital scans.



Implantology

Make use of various workflow options with Primescan and Omnicam for both implant surgery as well as implant prosthetics and directly connect to great partners such as Simplant, Atlantis and Azento.

SCAN



Sleep Appliance

Use your intraoral scanner to expand your range of applications in the field of sleep appliances. Send the scan data to Panthera Dental or your preferred partner to order high quality customized sleep devices.

The right scanner for all your digital needs



Primescan – Engineered for superior performance

- Future-proof patented technology
- Full arch scan in less than a minute
- Easy scanning of deep cavities, steep inclines and shiny surfaces like metal crowns
- Simple scanning of large edentulous areas and palates
- Unique three sleeves concept



Omniscam AC – Proven reliability

- Best-selling scanner with the biggest community
- Successful allrounder for all relevant applications, with over 7 million impressions* per year
- Small scanner head for easiest access
- Real color scanning
- Great accuracy and performance

EASY TO USE

- Impression taking with Primescan and Omnicam is easy and intuitive, especially with the guided scanning option for full arch scan with Omnicam. This procedure can be delegated, saving time and bringing more joy to your assistants.

EXCELLENT SCAN RESULTS

- Reliable quality with Omnicam and outstanding accuracy with Primescan, both scanners ensure a perfect fit for any restoration or appliance. Plus, digital models are less prone to errors than analog casts and reduce the need of rework. Your laboratory will appreciate it.

TIME SAVING

- Easy and fast scans with shorter treatment time and immediate control of scan results lead to increased efficiency in the practice. Omnicam is great for quadrant scans and Primescan outstanding for full arch scans.

OUTSTANDING HYGIENE

- Primescan and Omnicam have both fully closed scanning windows to prevent liquid infiltration during the scanning process. The mobile acquisition center is approved as a medical device to be used in patient vicinity unlike to consumer notebooks. Closed surfaces for easy and fast disinfection. Plus, without physical models there is no risk of cross contamination.

* Source: Internal data

Dentsply Sirona

Sirona Dental Systems GmbH
Fabrikstraße 31, 64625 Bensheim, Deutschland
dentsplysirona.com

Procedural Solutions

Preventive
Restorative
Orthodontics
Endodontics
Implants
Prosthetics

Enabling Technologies

CAD/CAM
Imaging Systems
Treatment Centers
Instruments

THE DENTAL
SOLUTIONS
COMPANY™

